




### ■ Catalog number

Note that the catalog numbers for KSP ground spiral bevel gears have a different configuration compared to other miters and bevel gears.

**KSP 031 001 G U L**




### ■ Features of KSP spiral bevel gears

1. High-strength, high-precision product of JIS grade 0.
2. Superior performance with regard to high speed, low noise, and low vibration.
3. Module is 1.5 to 6
4. Gear ratio types are 1, 1.5 and 2

### ■ Shape

Shape for secondary operations (with margin)  
\* The parts ---- in the figure below are protected from carburizing.



### ■ Transmission capacity table

1. The values in the transmission capacity table below are where the service factor is 1. Be sure to correct the load torque according to the table on the right. The corrected load torque is calculated by multiplying the load torque applied to the output shaft by service factor (Sf).
2. When using at increased speed (where gear is drive and pinion is driven), the torque of the pinion is the value obtained by multiplying the value shown in the transmission capacity table by the speed ratio.

NOTE 1: When the speed ratio is 1/1.5, the pinion torque is 1/1.5 of the value shown in the transmission capacity table.

### ■ Service factor (Sf)

Impact from motor	Impact from load		
	Uniform load	Moderate impact	Severe impact
Uniform load (electric motor, turbine, hydraulic motor, etc.)	1.0	1.25	1.75
Mild impact (multi-cylinder engine)	1.25	1.5	2.0
Moderate impact (single-cylinder engine)	1.5	1.75	2.25

### ■ Transmission capacity table (speed ratio 1/1)

Upper transmission capacity (kw) Lower output torque (N·m)

Figure number	Rotational speed (rpm)							
	50	100	300	600	900	1200	1800	3000
KSP031001	0.035	0.068	0.195	0.375	0.548	0.716	1.04	1.65
	6.65	6.51	6.20	5.98	5.82	5.69	5.51	5.25
KSP040001	0.092	0.179	0.511	0.980	1.43	1.86	2.69	4.25
	17.6	17.2	16.3	15.6	15.2	14.8	14.3	13.5
KSP053001	0.211	0.412	1.17	2.23	3.25	4.22	6.08	9.55
	40.4	39.3	37.3	35.6	34.5	33.6	32.3	30.4
KSP066001	0.367	0.715	2.02	3.85	5.59	7.26	10.4	16.3
	70.2	68.3	64.4	61.4	59.3	57.8	55.4	52.0
KSP078001	0.577	1.12	3.16	6.00	8.68	11.2	16.1	25.1
	109.8	106.9	101.0	95.5	92.2	89.5	85.5	79.8
KSP092001	0.901	1.75	4.91	9.31	13.5	17.4	24.9	38.6
	172.6	166.7	156.9	148.1	143.2	138.3	132.4	122.6
KSP105001	1.44	2.78	7.80	14.7	21.2	27.4	39.1	60.3
	274.6	265.8	248.1	234.4	225.6	218.7	207.9	192.2
KSP132001	2.33	4.50	12.6	23.6	34.0	43.7	62.0	95.0
	445.2	430.5	400.1	376.6	360.9	348.1	329.5	302.0
KSP157001	3.68	7.10	19.7	37.0	53.0	68.1	96.2	146
	704.1	678.6	628.6	589.4	562.9	542.3	510.9	466.8
KSP184001	5.31	10.2	28.3	52.8	75.5	96.8	136	206
	1010	976.7	901.2	841.4	801.2	770.8	722.8	656.1

### ■ Transmission capacity table (speed ratio 1/1.5)

Upper transmission capacity (kw) Lower output torque (N·m)

Figure number	Rotational Speed of Pinion (rpm)							
	50	100	300	600	900	1200	1800	3000
KSP0481.5	0.077	0.151	0.432	0.830	1.21	1.58	2.29	3.64
	22.2	21.6	20.6	19.8	19.3	18.9	18.2	17.4
KSP0611.5	0.159	0.309	0.882	1.69	2.46	3.21	4.64	7.33
	45.4	44.3	42.2	40.4	39.2	38.3	37.0	35.0
KSP0741.5	0.277	0.540	1.53	2.93	4.27	5.55	8.00	12.6
	79.4	77.4	73.4	70.1	68.0	66.3	63.7	60.1
KSP0901.5	0.466	0.908	2.57	4.90	7.12	9.24	13.3	20.8
	133.4	130.4	122.6	116.7	113.8	110.8	105.9	99.0
KSP1051.5	0.700	1.36	3.84	7.31	10.6	13.7	19.7	30.7
	201.0	195.2	183.4	174.6	168.7	163.8	156.9	147.1
KSP1241.5	1.03	2.00	5.63	10.7	15.5	20.0	28.6	44.5
	295.2	286.4	268.7	255.0	246.1	239.3	227.5	212.8
KSP1411.5	1.56	3.03	8.51	16.1	23.2	30.1	42.9	66.4
	448.2	434.4	406.0	384.4	370.7	358.9	341.3	317.7
KSP1631.5	2.27	4.39	12.3	23.2	33.4	43.1	61.4	94.6
	650.2	628.6	587.4	554.1	532.5	514.8	489.4	452.1
KSP1811.5	2.92	5.64	15.8	29.7	42.7	55.1	78.3	120
	836.5	809.0	754.1	710.0	680.6	658.0	623.7	574.7

### ■ Transmission capacity table (speed ratio 1/2)

Upper transmission capacity (kw) Lower output torque (N·m)

Figure number	Rotational Speed of Pinion (rpm)							
	50	100	300	600	900	1200	1800	3000
KSP039002	0.025	0.049	0.142	0.275	0.404	0.528	0.770	1.23
	9.63	9.45	9.07	8.76	8.57	8.41	8.17	7.83
KSP056002	0.075	0.147	0.423	0.814	1.19	1.55	2.26	3.59
	28.8	28.1	27.0	26.0	25.3	24.8	23.9	22.8
KSP075002	0.185	0.361	1.03	1.98	2.89	3.76	5.45	8.61
	70.7	69.0	65.7	63.1	61.3	59.9	57.9	54.8
KSP096002	0.364	0.710	2.02	3.86	5.62	7.31	10.5	16.6
	139.3	135.3	128.5	122.6	119.6	116.7	111.8	105.9
KSP119002	0.649	1.26	3.58	6.82	9.90	12.9	18.5	29.0
	248.1	241.2	227.5	217.7	209.9	205.0	196.1	184.4
KSP145002	1.07	2.08	5.87	11.2	16.2	21.0	30.1	46.9
	408.9	397.2	373.6	356.0	343.2	333.4	319.7	298.1
KSP172002	1.78	3.45	9.72	18.4	26.6	34.5	49.3	76.5
	680.6	660.0	618.8	587.4	565.8	549.2	523.7	487.4




# Ground Spiral Bevel Gears




Specifications	
Precision grade	JIS B 1704: 1978 grade 0
Gear teeth	Gleason
Pressure angle	20°
Helix angle	35°
Material	SCM415*
Heat treatment	Carburized (Bore and hub are carburized)
Tooth hardness	60 to 63HRC**


\* The material of module 3.5 and above is SCM420.  
\*\* Modules 1.5 and 2 have the tooth hardness of 80 to 83 HRA.




A



A'



B



C

Catalog Number	Gear Ratio	Module	No. of teeth	Direction of spiral	Pitch dia.	Face width	Shape	Outside dia.	Holder surface dia.	Bore	Hub dia.	Hole length
								A	B	CH7	D	E
KSP031001GU L KSP031001GU R	1	m1.5	20	L R	30	7	A	30.5	16.5	10	22	13
KSP040001GU L KSP040001GU R		m2	20	L R	40	9	B	40	22.5	12	31	14
KSP078001GU L KSP078001GU R		m3.5	22	L R	77	18	B	78	43	20	54	27
KSP105001GU L KSP105001GU R		m4.5	23	L R	103.5	25	C	105	50	26	70	35
KSP132001GU L KSP132001GU R		m5	26	L R	130	29	C	132	64	30	82	41
KSP157001GU L KSP157001GU R		m5.5	28	L R	154	34	C	157	76	32	92	47
KSP184001GU L KSP184001GU R		m6	30	L R	180	38	C	184	84	40	101	51
KSP0481.5GU P KSP0481.5GU G		1.5	m2	16 24	L R	32 48	9	A' B	34 48	17.5 30	10 12	24 30
KSP0741.5GU P KSP0741.5GU G	m2.75		18 27	L R	49.5 74.25	15	A' B	52 74	27 44.5	14 20	40 50	20 25
KSP075002GU P KSP075002GU G	2	m2.5	15 30	L R	37.5 75	14	A' C	40 75	20 36	12 16	30 44	17 24
KSP096002GU P KSP096002GU G			m3	16 32	L R	48 96	18	B C	53 96	23.5 46	12 20	36 56
KSP119002GU P KSP119002GU G		m3.5		17 34	L R	59.5 119	22	A C	65 119	34 54	16 26	44 63

Hub width	Total length	Mounting distance	Machinable MAX bore	Allowable torque (kgf-m)	Backlash (mm)	Weight (kg)	Catalog Number
F	G	H					
6	15	25	12	0.61	0 ~0.05	0.04	KSP031001GU L KSP031001GU R
7	16.5	30	16	1.59	0 ~0.05	0.09	KSP040001GU L KSP040001GU R
12	32	57	32	9.74	0.05~0.10	0.59	KSP078001GU L KSP078001GU R
14	39	72	40	23.9	0.05~0.10	1.33	KSP105001GU L KSP105001GU R
14	45	88	48	38.4	0.05~0.10	2.49	KSP132001GU L KSP132001GU R
20	53.5	105	55	60.1	0.05~0.10	3.90	KSP157001GU L KSP157001GU R
17	56.5	118	62	85.8	0.05~0.10	5.79	KSP184001GU L KSP184001GU R
4.5 7	14.5 19	31 30	— 20	2.02	0 ~0.05	0.05 0.14	KSP0481.5GU P KSP0481.5GU G
6 12	22 29	46 45	20 35	7.15	0.05~0.10	0.20 0.49	KSP0741.5GU P KSP0741.5GU G
4.5 11	19.5 25.5	44 38	14 25	6.43	0.05~0.10	0.10 0.44	KSP075002GU P KSP075002GU G
2.5 12	21.5 31	53 47	19 32	12.5	0.05~0.10	0.20 0.91	KSP096002GU P KSP096002GU G
3.6 15	27.5 35.5	67 55	25 40	22.2	0.05~0.10	0.36 1.45	KSP119002GU P KSP119002GU G

Spur Gears  
Helical Gears  
Internal Gears  
Racks  
CP Racks & Pinions  
Miter Gears  
Bevel Gears  
Screw Gears  
Worm Gears  
Gearboxes  
Other Products

Spur Gears  
Helical Gears  
Internal Gears  
Racks  
CP Racks & Pinions  
Miter Gears  
Bevel Gears  
Screw Gears  
Worm Gears  
Gearboxes  
Other Products