





Specifications	
Precision grade	JIS B 1704: 1978 grade 3
Gear teeth	Gleason
Pressure angle	20°
Material	S45C
Heat treatment	—
Tooth hardness	(less than 194HB)



Catalog No.	Gear ratio	Module	No. of teeth	Shape	Bore		Pitch dia.	Outside dia.	Mounting distance	Total length	Crown to back length		Hub width
					A _{H7}	B					G	H	
SM2-16	1	m2	16	B2	10	27	32	34.83	30	19	15.41	11.5	
SM2.5-16		m2.5	16	B2	12	34	40	43.53	35	21	16.77	12	
SM3-16		m3	16	B2	14	42	48	52.24	40	23	18.12	13	
SM4-16		m4	16	B2	16	55	64	69.66	50	28	20.83	13.5	
SM5-16		m5	16	B2	20	70	80	87.07	65	37	28.54	20	
SM1-20	1	m1	20	B3	6	16	20	21.41	20	13.94	10.71	8	
SM1.25-20		m1.25	20	B3	8	22	25	26.77	23	15.27	11.38	9	
SM1.5-20		m1.5	20	B3	8	26	30	32.12	30	21.24	16.06	13	
SM2-20		m2	20	B3	12	34	40	42.83	37	24.89	18.41	14	
SM2.5-20		m2.5	20	B3	14	42	50	53.54	48	32.54	24.77	19	
SM3-20	1	m3	20	B3	16	50	60	64.24	58	39.84	30.12	23	
SM3.5-20		m3.5	20	B3	20	60	70	74.95	65	44.13	32.47	25	
SM4-20		m4	20	B3	20	64	80	85.65	75	50.78	37.83	27	
SM5-20		m5	20	B3	25	80	100	107.07	90	60.38	43.54	30	
SM6-20		m6	20	B3	28	100	120	128.48	104	67.67	48.24	34	
SM8-20	m8	20	B3	30	130	160	171.31	125	73.33	50.66	30		
SM1-25	1	m1	25	B3	6	20	25	26.41	23	15.16	11.21	8	
SM1.25-25		m1.25	25	B3	8	25	31.25	33.02	28	17.88	13.26	9.25	
SM1.5-25		m1.5	25	B3	10	30	37.5	39.62	34	22.25	16.31	11.5	
SM2-25		m2	25	B3	12	40	50	52.83	40	24.33	16.41	10	
SM2.5-25		m2.5	25	B3	16	50	62.5	66.04	50	30.41	20.52	12.5	
SM3-25	1	m3	25	B3	20	60	75	79.24	60	37.81	24.62	15	
SM3.5-25		m3.5	25	B3	25	70	87.5	92.45	70	43.23	28.72	17.5	
SM4-25		m4	25	B3	28	80	100	105.66	80	49.32	32.83	20	
SM5-25		m5	25	B3	28	100	125	132.07	100	60.82	41.04	25	
SM6-25		m6	25	B3	28	120	150	158.48	120	72.32	49.24	30	
SM1-30	1	m1	30	B3	8	24	30	31.41	28	17.71	13.71	10	
SM1.25-30		m1.25	30	B3	10	30	37.5	39.27	36	23.47	18.13	13.5	
SM1.5-30		m1.5	30	B3	10	36	45	47.12	43	28.24	21.56	16	
SM2-30		m2	30	B3	12	45	60	62.83	50	29.42	21.41	12.5	
SM2.5-30		m2.5	30	B3	16	60	75	78.54	62	36.28	26.27	17	
SM3-30	1	m3	30	B3	20	70	90	94.24	75	45.47	32.12	20	
SM3.5-30		m3.5	30	B3	25	90	105	109.95	85	49.66	34.97	25	
SM4-30		m4	30	B3	28	100	120	125.66	95	54.52	37.83	25	
SM5-30		m5	30	B3	28	130	150	157.07	120	68.56	48.54	35	

Length of bore	Face width	Holding surface dia.	Allowable torque (N-m)		Allowable torque (kgf-m)		Backlash (mm)	Weight (kg)	Catalog No.
			Bending strength	Surface durability	Bending strength	Surface durability			
19	7	—	3.84	0.33	0.39	0.034	0.06~0.16	0.076	SM2-16 SM2.5-16 SM3-16 SM4-16 SM5-16
21	9	—	7.63	0.68	0.78	0.069	0.07~0.17	0.14	
23	11	—	13.3	1.21	1.36	0.12	0.08~0.18	0.22	
28	14	—	30.7	2.87	3.13	0.29	0.12~0.27	0.49	
37	17	—	58.9	5.62	6.00	0.57	0.14~0.34	1.03	
12	5	9.86	0.89	0.084	0.091	0.0086	0.03~0.13	0.019	SM1-20 SM1.25-20 SM3-20 SM4-20 SM5-20
13	6	13.03	1.70	0.16	0.17	0.017	0.04~0.14	0.036	
19	8	15.37	3.12	0.30	0.32	0.031	0.05~0.15	0.074	
22	10	21.72	7.13	0.72	0.73	0.073	0.06~0.16	0.15	
29	12	28.06	13.6	1.41	1.39	0.14	0.07~0.17	0.30	
35	15	31.57	24.1	2.54	2.45	0.26	0.08~0.18	0.53	SM3-20 SM3.5-20 SM4-20 SM5-20 SM6-20
40	18	39.09	38.8	4.15	3.96	0.42	0.10~0.25	0.82	
45	20	43.43	57.0	6.19	5.82	0.63	0.12~0.27	1.15	
54	26	54.46	114	12.6	11.6	1.29	0.14~0.34	2.15	
60	30	67.15	191	21.8	19.4	2.22	0.16~0.36	3.68	
62	35	95	413	49.6	42.1	5.06	0.20~0.45	7.05	SM8-20
14	6	15.03	1.47	0.16	0.15	0.017	0.03~0.13	0.035	SM1-25 SM1.25-25 SM3-25 SM4-25 SM5-25
16	7	18.7	2.75	0.31	0.28	0.032	0.04~0.14	0.063	
19	9	19.54	4.96	0.57	0.51	0.059	0.05~0.15	0.11	
20	12	26.06	11.8	1.41	1.20	0.14	0.06~0.16	0.22	
26	15	34.57	23.0	2.81	2.34	0.29	0.07~0.17	0.42	
32	20	37.43	42.1	5.24	4.29	0.53	0.08~0.18	0.74	SM3-25 SM3.5-25 SM4-25 SM5-25 SM6-25
37	22	46.77	64.7	8.19	6.60	0.83	0.10~0.25	1.15	
43	25	55.29	96.3	12.4	9.82	1.26	0.12~0.27	1.73	
50	30	65.15	184	24.2	18.7	2.47	0.14~0.34	3.41	
61	35	83	309	42.1	31.5	4.29	0.16~0.36	6.03	
16	6	19.03	1.99	0.26	0.20	0.026	0.03~0.13	0.057	SM1-30 SM1.25-30 SM3-30 SM4-30 SM5-30
21	8	22.37	4.05	0.54	0.41	0.055	0.04~0.14	0.12	
25	10	25.71	7.19	0.97	0.73	0.099	0.05~0.15	0.21	
25	12	36.06	15.9	2.22	1.62	0.23	0.06~0.16	0.37	
32	15	47.57	31.1	4.43	3.17	0.45	0.07~0.17	0.76	
40	20	53.43	57.5	8.33	5.87	0.85	0.08~0.18	1.32	SM3-30 SM3.5-30 SM4-30 SM5-30
45	22	67.77	88.0	13.0	8.97	1.32	0.10~0.25	2.20	
50	25	79.29	131	19.6	13.3	2.00	0.12~0.27	3.09	
62	30	99.15	249	38.3	25.4	3.91	0.14~0.34	6.47	

[Caution on Product Characteristics] ① The allowable torques shown in the table are the calculated values according to the assumed usage conditions. Please see page 253 for more details.
② Dimensions of the outside diameter, the overall length and crown to back length are all theoretical values, and some differences will occur due to the corner chamfering of the gear tips.

[Caution on Secondary Operations] ① Please read "Caution on Performing Secondary Operations" (Page 254) when performing modifications and/or secondary operations for safety concerns. KHK Quick-Mod Gears, the KHK's system for quick modification of KHK stock gears is also available.

* For products not categorized in our KHK Stock Gear series, custom gear production services with **short lead times** is available. For details see page 8.